


Comments:

1. For MSY14 Large Briefing (Divisible) – there is a Spectrum Industries Honors Lectern specified. There are several options available for this lectern. Will any options be required?
 - a. **RESPONSE**
 - i. **See Drawing AVMS09.B that was provided for reference during bid. Provide appropriate cutout as needed for cable cubby integration and for any other cutouts/grommets that the owner may require.. DMU to provide further direction as well as finish requirements.**
 - ii. Utilize Crisp Linen and edge band Silver North Sea, other selections are listed in the screen shot below

CUSTOMER APPROVAL SHEET (NSDS)

Please Email/Fax Approval back to Sales Rep

Product Type: Configured		Quote#: Q000247306
Item #: 37325-20008	Phantom Product	Ref Item #: 37325-BKSNB2211005
Description: Pivot Workstation 36,Crisp Linen-SNB		
Laminate:	WA 4942-38 Crisp Linen	
Edgeband:	Silver Northsea 3MM	
Metal Finish:	Black	
Leg Options:	Electric w/Foot Rest	
Worksurface:	Worksurface Cupholder 36"	
WS Accessories:	Storage Bin	
Modesty Panel:	Modesty Panel w/o Insert	
Modesty Panel Insert:	none	
Electrical Option:	Power Module White	
Wood Trim: n/a		Conceptual Drawing

2. There are two QSC items listed for many of the rooms that are no longer available, but QSC does offer alternate units.
 - a. Here are the original QSC units and proposed replacements. Can you confirm if the alternate units are approved?
 - i. A4MIO - alternate option QIO-ML4i & QIO-L4o
 - ii. I/O-22 - alternate option QIO-ML2x2
 - b. These units are in the following rooms
 - i. MSY07 308C7 (has I/O22)
 - ii. MSY09 317,316 (has I/O-22 & A4MIO)
 - iii. MSY10 multiple rooms (has I/O22)

- iv. MSY11 multiple rooms (has I/O22)
 - v. MSY12 317C1 (has I/O22)
 - vi. MSY15 409 (has A4MIO)
- c. **RESPONSE**
- i. **Any of the I/O22 devices can be replaced by the Axon A4FLEX**
 - ii. **Any D2FLEXio devices can be replaced with a QIO-ML2x2**
 - iii. **MSY08 317B1, 317B2, 317B5, 317B6, 317D1, 317D5 (has A4MIO)**
 - 1. **Replace with QIO-ML4i & run audio input for Digital Audio Interface (CAE device) from control room QIO-ML2x2(2) output**
 - iv. **MSY09 317C5,316 (only has A4MIO)**
 - 1. **Replace A4MIO with QIO-ML4i & run audio input for Digital Audio Interface (CAE device) from control room QIO-ML2x2(2) output**
 - v. **MSY10 Surgical Skills 317C2 & 317C4 (has I/O-22 & A4MIO)**
 - 1. **Replace A4MIO with QIO-ML4i & run audio input for Digital Audio Interface (CAE device) from control room QIO-ML2x2(2) output**
 - 2. **Replace I/O22 with A4FLEX**
 - vi. **MSY15 409 (has A4MIO)**
 - 1. **Replace with QIO-ML4i & QIO-L4o**